

## Counting scale KERN CPB





Note: Official verification duty for commercial trade

# Professional model, also with EC type approval [M], counting resolution up to 60,000 points

## **Features**

- · Precise counting: The automatic reference weight optimisation of reference weight gradually improves the average piece weight value
- Programmable using numerical key pad:
  - required reference quantity
  - known reference weight
- · Three displays for weight display, reference weight, total pieces
- · Counting results memory: adds up all individual piece counts, result is shown in total weight and total pieces
- Fill-to-target function: Target count or target weight can be programmed. When the target weight is reached there is an audible and visual signal
- · PRE-TARE function for manual subtraction of a known container weight, useful for checking fill-levels

- · High mobility: thanks to rechargeable battery operation (optional), compact, lightweight construction, it is suitable for the use in several locations (production, warehouse, dispatch department etc.)
- Two balances in one: Changes from counting mode to weighing mode at the touch of a key
- · Protective working cover included with delivery

## **Technical data**

- · Large backlit LCD displays, digit height 20 mm
- · Dimensions weighing surface, Stainless Steel, W×D 295×225 mm Overall dimensions W×D×H 315×350×105 mm
- · Net weight approx. 3,2 kg
- Permissible ambient temperature 0 °C/40 °C

## **Accessories**

- Protective working cover, scope of delivery: 5 items, KERN CFS-A02S05
- · Internal rechargeable battery pack, operating time up to 90 h without backlight, charging time approx. 12 h, KERN GAB-A04
- II Signal lamp for visual support of weighing with tolerance range, only in combination with, KERN CFS-A03
- · Y-cable for parallel connection of two terminal devices to the RS-232 interface on the scale, e.g. signal lamp and printer, KERN CFS-A04
- · Further details, plenty of further accessories and suitable printers see Accessories

STANDARD





























FACTORY
М
+3 DAYS
CPB-DM

Model	Weighing	Readability	Verification	Minimal load	Smallest part	Counting	Option			
	capacity		value		weight	resolution	Verification DAkkS Calibr.		DAkkS Calibr. Ce	rtificate
	[Max]	[d]	[e]	[Min]	[Normal]		MIII		DAkkS	
KERN	kg	g	g	g	g/piece	Points	KERN		KERN	
CPB 6K0.1N	6	0,1	-	-	1	60.000	-		963-128	
CPB 15K0.2N	15	0,2	-	-	2,5	60.000	-		963-128	
CPB 30K0.5N	30	0,5	-	-	5	60.000	-		963-128	

Dual-range balance switches automatically to the next largest weighing capacity [Max] and readibility [d]

Note: For applications that require verification, please order verification at the same time, initial verification at a later date is not possible.

Verification at the factory, we need to know the full address of the location of use.									
CPB 6K1DM	3   6	1   2	1   2	20	1	60.000	965-228	963-128	
CPB 15K2DM	6   15	2   5	2   5	40	2,5	60.000	965-228	963-128	
CPB 30K5DM	15   30	5   10	5   10	100	5	60.000	965-228	963-128	

Tel.: 03303 / 504066

Fax: 03303 / 504068

## **Pictograms**



#### Internal adjusting:

Quick setting up of the balance's accuracy with internal adjusting weight (motordriven)



## Adjusting program CAL:

For quick setting up of the balance's accuracy. External adjusting weight required



#### Easy Touch:

Suitable for the connection, data transmission and control through PC, tablet or smartphone.



#### Memory:

Balance memory capacity, e.g. for article data, weighing data, tare weights, PLU etc.



#### Alibi memory:

Secure, electronic archiving of weighing results, complying with the 2014/31/EU standard



#### Data interface RS-232:

To connect the balance to a printer, PC or network



#### RS-485 data interface:

To connect the balance to a printer, PC or other peripherals. Suitable for data transfer over large distances. Network in bus topology is possible



#### USB data interface:

To connect the balance to a printer, PC or other peripherals



#### Bluetooth\* data interface:

To transfer data from the balance to a printer, PC or other peripherals



#### WiFi data interface:

To transfer data from the balance to a printer, PC or other peripherals



#### Control outputs (optocoupler, digital I/O):

To connect relays, signal lamps, valves, etc.



## Analogue interface:

to connect a suitable peripheral device for analogue processing of the measurements



#### Interface for second balance:

For direct connection of a second balance



#### Network interface:

For connecting the scale to an Ethernet network



#### **KERN Communication Protocol (KCP):**

It is a standardized interface command set for KERN balances and other instruments, which allows retrieving and controlling all relevant parameters and functions of the device. KERN devices featuring KCP are thus easily integrated with computers, industrial controllers and other digital systems



#### GLP/ISO log:

The balance displays serial number, user ID, weight, date and time, regardless of a printer connection



# GLP/ISO log:

With weight, date and time. Only with KERN printers



#### Piece counting:

Reference quantities selectable. Display can be switched from piece to weight



#### Recipe level A:

The weights of the recipe ingredients can be added together and the total weight of the recipe can be printed out



#### Recipe level B:

Internal memory for complete recipes with name and target value of the recipe ingredients. User guidance through display



#### Totalising level A:

The weights of similar items can be added together and the total can be printed out



#### Percentage determination:

Determining the deviation in % from the target value (100 %)



# Weighing units:

Can be switched to e.g. nonmetric units at the touch of a key. See balance model. Please refer to KERN's website for more details



## Weighing with tolerance range:

(Checkweighing) Upper and lower limiting can be programmed individually, e.g. for sorting and dosing. The process is supported by an audible or visual signal, see the relevant model



# Hold function:

(Animal weighing program) When the weighing conditions are unstable, a stable weight is calculated as an average value



# Protection against dust and water splashes IPxx:

The type of protection is shown in the pictogram



#### Suspended weighing:

Load support with hook on the underside of the balance



#### **Battery operation:**

Ready for battery operation. The battery type is specified for each device



#### Rechargeable battery pack:

Rechargeable set



#### Universal mains adapter:

with universal input and optional input socket adapters for A) EU, CH, GB; B) EU, CH, GB, USA; C) EU, CH, GB, USA, AUS



#### Mains adapter:

230V/50Hz in standard version for EU, CH. On request GB, USA or AUS version available



#### Power supply:

Integrated in balance. 230V/50Hz standard EU. More standards e.g. GB, USA or AUS on request



# Weighing principle: Strain gauges:

Electrical resistor on an elastic deforming body



#### Weighing principle: Tuning fork:

A resonating body is electromagnetically excited, causing it to oscillate



# Weighing principle: Electromagnetic force compensation:

Coil inside a permanent magnet. For the most accurate weighings



# Weighing principle: Single cell technology:

Advanced version of the force compensation principle with the highest level of precision



#### Verification possible:

The time required for verification is specified in the pictogram



# DAkkS calibration possible (DKD):

The time required for DAkkS calibration is shown in days in the pictogram



### Factory calibration (ISO):

The time required for Factory calibration is shown in days in the pictogram



#### Package shipment:

The time required for internal shipping preparations is shown in days in the pictogram



## Pallet shipment:

The time required for internal shipping preparations is shown in days in the pictogram

# KERN - Precision is our business

To ensure the high precision of your balance KERN offers you the the appropriate test weight in the international OIML error limit classes E1-M3 from 1 mg - 2500 kg. In combination with a DAkkS calibration certificate the best pre-requisite for proper

The KERN DAkkS calibration laboratory today is one of the most modern and bestequipped DAkkS calibration laboratories for balances, test weights and force-measure-

Thanks to the high level of automation, we can carry out DAkkS calibration of balances, test weights and force-measuring devices 24 hours a day, 7 days a week.

#### . . .

- DAkkS calibration of balances with a maximum load of up to 50 t
- DAkkS calibration of weights in the range of 1 mg 2500 kg
- Volume determination and measuring of magnetic susceptibility (magnetic characteristics) for test weights
- Database supported management of checking equipment and reminder service
- Calibration of force-measuring devices
- DAkkS calibration certificates in the following languages DE, EN, FR, IT, ES, NL, PL
- $\boldsymbol{\cdot}$  Conformity evaluation and reverification of balances and test weights

# Your KERN specialist dealer:

ICS Schneider Messtechnik GmbH Briesestraße 59 D-16562 Hohen Neuendorf / OT Bergfelde

Tel.: 03303 / 50 40 66 Fax: 03303 / 50 40 68

info@ics-schneider.de www.ics-schneider.de

<sup>\*</sup>The Bluetooth® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by KERN & SOHN GmbH is under license. Other trademarks and trade names are those of their respective owners.